## **VACTEST PPP 700 D**

Measuring device for food packaging processes





## **Packageable**

Specially designed for direct use in food packaging processes, can be placed inside the packaging and be packaged, robust and compact construction

## **High performance**

Excellent measurement accuracy due to Piezo-Pirani combination sensor, great measurement range (1,200 - 0.01 mbar)

## **Intuitive operation and handling**

Easy control via five buttons, easy-to-read display, integrated li-ion battery, rechargeable via USB-C

www.buschvacuum.com © Busch Vacuum Solutions 13.02.2024 1/2

# **VACTEST PPP 700 D**

Measuring device for food packaging processes



	VACTEST PPP 700 D
Measurement principle	Piezoresistive / Pirani
Measurement range	1200–0.01 mbar
Resolution	1200–1 mbar: 0.1 mbar , 0.99–0.01 mbar: 0.01 mbar
Measurement uncertainty	1200–40 mbar: 0.3% full scale , 40–0.01 mbar: 10% of reading
Measurement interval	0.02-60 s
Supply voltage	Internal rechargeable lithium-ion battery
Min. battery operating time	48 h
Serial interface	USB-C and Bluetooth
Display	LCD graphic display, resolution 400 x 240 px
Operating temperature	+5 +50 °C
Weight approx.	170 g
Dimensions (L x W x H)	105 x 70 x 25.4 mm
Vacuum connection	Sensor flush mounted in housing, G 1/8" female thread for calibration

## **DO YOU WANT TO KNOW MORE?**

Get in touch with us directly! sales@busch.ae or +971 6552 8654





**CALL NOW** 

www.buschvacuum.com © Busch Vacuum Solutions 13.02.2024 2/2