

VACTEST DPH 400

Digital transmitter



Intelligent

Extended measurement range (1000 to $5 \cdot 10^{-10}$ mbar), state-of-the-art microcontroller technology, fully customizable parameters

Reliable

High industrial standards, robust design, Bayard-Alpert principle with double filaments for extended lifetime and high reliability

Efficient

Modular design, plug and play sensor for maximum uptime

Accessories, spare parts and options

- Replacement sensor
- Active Sensor Controller
- Connecting cable
- RS485 interface converter to Bluetooth
- RS485 interface converter to USB
- Electrical power supply
- Calibration certificate
- VACTEST Explorer Pro

VACTEST DPH 400

Digital transmitter



	VACTEST DPH 400	VACTEST DPH 400	VACTEST DPH 400
Measurement principle	Pirani / Bayard-Alpert	Pirani / Bayard-Alpert	Pirani / Bayard-Alpert
Materials exposed to vacuum	Stainless steel 1.4307, Ni, W, Pt, yttrium coated iridium, glass	Stainless steel 1.4307, Ni, W, Pt, yttrium coated iridium, glass	Stainless steel 1.4307, Ni, W, Pt, yttrium coated iridium, glass
Number of filaments	1 (Pirani) / 2 (Bayard-Alpert)	1 (Pirani) / 2 (Bayard-Alpert)	1 (Pirani) / 2 (Bayard-Alpert)
Filament material	Tungsten (Pirani) / yttrium coated iridium (Bayard-Alpert)	Tungsten (Pirani) / yttrium coated iridium (Bayard-Alpert)	Tungsten (Pirani) / yttrium coated iridium (Bayard-Alpert)
Measurement range	1000–5 · 10 ⁻¹⁰ mbar	1000–5 · 10 ⁻¹⁰ mbar	1000–5 · 10 ⁻¹⁰ mbar
Overpressure limit	4 bar abs.	4 bar abs.	4 bar abs.
Measurement uncertainty	< 30% of reading (1000–10 mbar), < 10% of reading (10 ⁻¹ · 10 ⁻⁸ mbar)	< 30% of reading (1000–10 mbar), < 10% of reading (10 ⁻¹ · 10 ⁻⁸ mbar)	< 30% of reading (1000–10 mbar), < 10% of reading (10 ⁻¹ · 10 ⁻⁸ mbar)
Repeatability of measurement	±2% of reading (10 ⁻¹ · 10 ⁻² mbar), ±5% of reading (1 · 10 ⁻² –1 · 10 ⁻⁸ mbar)	±2% of reading (10 ⁻¹ · 10 ⁻² mbar), ±5% of reading (1 · 10 ⁻² –1 · 10 ⁻⁸ mbar)	±2% of reading (10 ⁻¹ · 10 ⁻² mbar), ±5% of reading (1 · 10 ⁻² –1 · 10 ⁻⁸ mbar)
Leakage rate	< 5 · 10 ⁻¹⁰ mbar · l/s	< 5 · 10 ⁻¹⁰ mbar · l/s	< 5 · 10 ⁻¹⁰ mbar · l/s
Reaction time	< 50 ms	< 50 ms	< 50 ms
Serial interface	RS485	RS485	RS485
Electrical connection	D-Sub, 15 poles, male	D-Sub, 15 poles, male	D-Sub, 15 poles, male
Supply voltage	20–30 V	20–30 V	20–30 V
Max. power consumption	9 W (relays)	9 W (relays)	9 W (relays)
Output signal	0–10 V, RS485	0–10 V, RS485	0–10 V, RS485
Setpoint relay	2 dry contacts	2 dry contacts	2 dry contacts
Relay contact rating	2A, 50 VAC / 2A, 30 VDC, max. 60 VA	2A, 50 VAC / 2A, 30 VDC, max. 60 VA	2A, 50 VAC / 2A, 30 VDC, max. 60 VA
Operating temperature	+5 ... +60 °C	+5 ... +60 °C	+5 ... +60 °C
Max. bake-out temperature	180 °C	180 °C	180 °C
Weight approx.	475 g	475 g	475 g
Dimensions (L x W x H)	45 x 66 x 141 mm	45 x 66 x 141 mm	45 x 66 x 141 mm
Vacuum connection	DN 25 ISO-KF	DN 40 ISO-KF	DN 40 CF-F
Display	Without display	Without display	Without display

DO YOU WANT TO KNOW MORE?

Get in touch with us directly!
busch@buschvacuum.hu or +36 24 887 308



CONTACT FORM



CALL NOW